WARRANTY

All fiber optic transmission systems, products and accessories manufactured by Liteway, Inc. and it's subsidiaries are fully tested prior to shipment and are warranted against defective materials and workmanship for a period of five full years from the date of the original shipment. Should a problem occur, a Return Material Authorization Number (RMA) must be obtained from Liteway Inc. at (516) 931-2800 and the item returned to Liteway, Inc. 166 Haverford Road, Hicksville, NY 11801, USA, prepaid. Liteway Inc. will then, at its option repair or replace the defective item.

Liteway, Inc. maximum liability under this warranty is limited to the cost of the defective item only. No contingent liabilities of any kind are either assumed or implied.

Any items returned to Liteway, Inc. that have been misused, abused, damaged, modified, connected or adjusted in any way contrary to the instructions furnished by Liteway, Inc. or repaired by unauthorized personnel will not be covered by this warranty. Any non-warranty repairs required will be quoted at the current rate for such services.



Important Notices



CAUTION! AVOID DIRECT EXPOSURE TO BEAM.

All -7,-8, and -9 Models use laser diodes. These solid-state laser diodes are located in the optical ports of these units. Laser diodes produce invisible radiation that may be harmful to human eyes. Never look directly into the optical port of any fiber optic unit designed to operate with single-mode optical fiber.

NOT FOR LIFE SUPPORT SYSTEMS

Liteway, Inc. does not authorize or warrant any of its products or accessories for use in critical life support systems or applications of any kind.

OPERATING INSTRUCTIONS

LuxLink® Optical to Electrical Converter

Model OE-1001

The *LuxLink*® OE-1001 is an amplified analog optical to electrical converter that is utilized to view optical signals present in a fiber optic cable. It is useful for research and development applications as well as for routine troubleshooting.



Technical Specifications

50 KHz to 1.5 GHz (-3dB)			
< 1 nsec for -3, -7 models			
< 2 nsec for -1 models			
0 dBm (1000uW) @850nm			
-3 dBm (500uW) @1310/1550 nm			
-20 dBm (10uW) rms @ 850nm			
-23 dBm (5uW) rms @ 1310/1550nm			
20 dB usable			
ST (-1, -3) FCPC (-7)			
1V peak to peak at max optical input			
50 Ohms			
660,850, 1310 or 1550nm			
Power, Signal			
BNC			
-35° to +75°C			
11-24 VAC/DC @250ma			
5.0"(127)L x 1.0" (25.4)W x 3.0"(7)D			


All specifications are subject to change without prior notice.



www.LuxLink.com USA 516-931-2800

Installation Instructions

The below diagram shows a typical use of the OE-1001 electrical to optical converter.



Two wavelength rages are available. The sensitivity of these ranges are as follows;

Models OE-1001-3 & -7		
λ	Sensitivity	
1550nm	> 100 mV/mW	
1310nm	> 80 mV/mW	
850nm	> 10 mV/mW	

Model OE-1001-1		
λ	Sensitivity	
850nm	> 40 mV/mW	
660nm	> 20 mV/mW	

Power Terminal Block Connections

Pin	Function
1	Alarm output for use with optional Alarm Sensing Unit
	ALM-1000. No other connections should be made to this
	terminal
2	+11 to 24 DC or AC Volts input
3	AC or DC return (Common to Housing)

Be certain to check all connections, settings and voltages before applying power

Indicator Lights

Integral indicators are provided to monitor repetitive signals as well as the presence of operating power making system troubleshooting simple.

Indicator	Lights when
Pwr	Proper power is present.
Alrm	The loss of signal alarm is activated and there is no video present.
Sig	A data signal is being received.

The **Alarm** switch is used to turn the alarm function on and off.

